

MODEL 275E SPARE PARTS LIST

Level A, Consumable Parts:

4980-0328	Filter, 2-Micron Woven SS 9" Lg. (Other Options Available)
4904-0016	O-Ring, Viton 2-217, Filter Cap
4904-0036	O-Ring, Viton 2-318, Filter Cap
4904-0046	O-Ring, Viton 2-110, Chamber Manifold to Chamber Body
4904-0002	O-Ring, Viton 2-113, Isolation Valve Body to Chamber Manifold
8010-0011	Silicone Grease – 700°F High Temperature 1oz. (For O-Rings)

Level B, Basic Parts:

3014-0054	Heater Element, 4-1/4" Lg. 120VAC @ 250Watt
3014-0058	Heater Element, 4-1/4" Lg. 120VAC @ 125Watt
3103-0014	Temp. Switch Heater Control, Normally Closed Below 340°F
OR	
3103-0061	Temp. Switch Heater Control, Normally Closed Below 375°F
5600-0128	Temperature Controller, 1/32 DIN
1150-0053	Thermocouple, Type "K" (Filter Heater Temp. Control/Monitoring)
OR	
1150-0059	Temp. Sensor, RTD PT100 (Filter Heater Temp. Control/Monitoring)
3152-0003	Solid State Relay, 120/240VAC Control/240VAC Drive 25-Amp
3152-0002	Solid State Relay, 3-32VDC Control/240VAC Drive 25-Amp
3103-0012	Low Temp. Switch, Normally Open Below 225°F (Fail Safe)
OR	
3103-0013	Low Temp. Switch, Normally Closed Below 225°F
4955-0131	Solenoid Valve, 3-Way 115VAC (Isolation Valve Control)
OR	
4955-0132	Solenoid Valve, 3-Way 24VDC (Isolation Valve Control)
OR	
4955-0140	Solenoid Valve, 3-Way 230VAC (Isolation Valve Control)
4955-0136	Solenoid Valve, 2-Way 115VAC (Blowback Control)
OR	
4955-0137	Solenoid Valve, 2-Way 24VDC (Blowback Control)
OR	
4955-0144	Solenoid Valve, 2-Way 230VAC (Blowback Control)
4955-0148	Check Valve, Set @ 3PSIG
3014-0066	Enclosure Heater, 115VAC @ 250Watt
OR	
3014-0067	Enclosure Heater, 230VAC @ 300Watt
3103-0013	Temp. Switch, Enclosure Heater, Normally Closed Below 225°F
OR	
3103-0014	Temp. Switch, Enclosure Heater, Normally Closed Below 340°F

MODEL 275E SPARE PARTS LIST CONTINUED

3600-0019	Blowback Timer Card, 115VAC (NA w/ Enclosure Heater)
OR	
3600-0054	Blowback Timer Card, 230VAC (NA w/ Enclosure Heater)
5150-0157	Insulation Blanket for Heated Filter Assembly
5209-1001	Filter Cap, 316 SS Assembly w/ SS Woven Filter
5209-1010	Filter Cap, Hast-C276 Assembly w/ SS Woven Filter
5209-0180	Isolation Valve Assembly, Air Op. "Normally Open"
or	
5209-0207	Isolation Valve Assembly, Air Op. "Normally Closed"